

A DIVISION OF AHRENS AGRICULTURAL INDUSTRIES, INC. BOX 686 GRINNELL, IOWA 50112 PHONE 641-236-5822 TOLL FREE 1-800-541-7866 FAX 1-641-236-3341 www.Miraco.co

SPECIFICATIONS


PART 1 - GENERAL


- A. DESCRIPTION:
 - 1. EquiFount is designed for small numbers of livestock to be bolted on a wall in the corner. A pressurized water source is required. Electrically heated model available #1100.
- B. WEIGHTS & DIMENSIONS:

Model #	Gallons	Description	Dimensions		Weight
1100	1	Non-heated	16" x 16" x 14"	40.64 x 40.64 x 35.56 cm	16#
1100	1	Heated	16" x 16" x 14"	40.64 x 40.64 x 35.56 cm	16#
1200	1	Wallmount	16" x 16" x 14"	40.64 x 40.64 x 35.56 cm	17#
1200	1	Electric Wallmount	16" x 16" x 14"	40.64 x 40.64 x 35.56 cm	17#

- C. MATERIAL NECESSARY FOR INSTALLATION:
 - 1. 1/2" x 3" galvanized lags or bolts.
 - 2. #834-5 insulated tube.
- PART II MATERIALS, PRODUCTS
 - A. MATERIALS:
 - 1. Polyethylene.
 - B. VALVE:
 - 1. Miraco plastic plunger style valve.








Warm Climate Use


Water line from above should be protected with the pipe sleeve or wood.


Use 1/2" x 3" lags or bolts (galvanized). Lags are easiest if there is nothing on the other side of the studs, otherwise use galvanized bolts. Put nuts on the inside.

Distance from the floor at the owners discretion.



Water Level Adjustment





When installing heat cable above do not wrap.